

INSTALLATION INSTRUCTIONS

159 wasaga
Nov 9/21

PREPARING THE ENCLOSURE

Gloves and safety goggles should be worn during installation.

It is not recommended to install the appliance into a corner or directly beside a wall. The door will need to be opened more than 90° to allow full extension of the shelves. If it is necessary to place the unit next to a wall or in a corner, leave at least 2-4 inches (5-10 cm) of space between the wall and the appliance to allow for the door opening.


The cabinet opening must be at least 24 inches (61 cm) wide by 35 inches (88.9 cm) high by 25 inches (63.5 cm) deep.

Note: The listed depth requirement is assuming that the electrical outlet is located in the adjacent cabinetry or flush mounted in the rear wall, not surface mounted inside the enclosure.


If the electrical outlet is located inside adjacent cabinetry, cut a 1.5 inch (3.8 cm) diameter hole to admit the power cord. If the cabinet wall is metal, the hole edge must be covered with a bushing or grommet.

REQUIRED TOOLS

- Safety goggles
- Gloves
- Tape measure
- Carpenter square
- Level
- Flashlight
- Electric drill with hole bit




Bar Fridge



159 warrage
Nov 7/21

[Home \(/\)](#) > [Appliances \(/collections/appliances\)](#) > [Kitchen \(/collections/appliances-kitchen\)](#) > [Microwaves \(/collections/appliances-kitchen-microwaves\)](#)

Whirlpool®



Whirlpool Stainless Steel Countertop Microwave (1.6 Cu. Ft.) - YWMC30516HZ

★★★★★ (40) [Write A Review](#)

SKU: 13230014 [Special Order](#)

[Local Delivery Available - Details](#)

[Special Order Item: Non-Cancellable](#)

[60 Day Low Price Guarantee - Details](#)

\$ 309.00

 [ADD TO CART](#)

 [Wishlist](#)

INSTALLATION INSTRUCTIONS

159
waga
Nov 9/21






Tools and Parts

Tools Needed

Gather the required tools and parts before starting installation. Read and follow the instructions provided with any tools listed here.

- Measuring tape
- Pencil
- Phillips screwdriver
- Drill
- 7/64" drill bit

Parts Supplied (not shown to scale)


		
Rails (2)	Bottom duct	Trim kit frame
		
Short screws (14) (11 + 3 extra)		Long wood screws (6 - painted) (4 + 2 extra)

Location Requirements

The microwave oven may be installed over a built-in oven. If installing over a built-in oven, make sure there is a minimum of 3" (7.6 cm) between the top of the lower oven cutout and the microwave oven cutout floor.


The microwave oven may also be installed in a cabinet by itself (without a built-in oven below). For best usability, we recommend a minimum distance of 36" (91.4 cm) from the floor to the cutout floor.

Make sure the surrounding cabinetry has clearance to open and close freely. Allow a clearance of at least 1 3/8" (4.0 cm) below the cutout floor (3" (7.6 cm) for installation above a built-in oven), and a clearance of at least 2" (5.1 cm) above the cutout opening.



A. Upper cabinet
B. Microwave oven cutout
C. Lower oven cutout
D. Lower cabinets
E. Floor

Required Cutout Dimensions




A. Trim kit frame overhang
B. Cutout for lower oven

NOTES:

- Height dimension is critical: 17" (43.2 cm) minimum, 17 1/8" (43.5 cm) maximum.
- Width and depth measurements have ±1/16" (2 mm) tolerance.
- 3" (7.6 cm) minimum dimension is from lower oven cutout ceiling to microwave oven cutout floor.
- Trim kit frame extends 1 1/8" (2.7 cm) above and below the cutout opening.

Trim Kit Frame Dimensions



27" (68.6 cm) trim kit
2 3/8" (5.2 cm) height

AVG


30" Wall mounted hood - MSRP: \$929.00

The information contained herein is based on sources that we believe to be reliable, but is not guaranteed by us, may be incomplete or may change without notice


159 Wasaga

AVH-308CS/368CS

Dimensions



Installation



A	Floor to ceiling height	variable
B	Floor to counter top height (standard)	36"
C	Recommended height between cooking surface and bottom of the hood	28" to 30"
D	Hood height	2.36"
E	Chimney height	Max 44.63"

Duct transition



The information contained herein is based on sources that we believe to be reliable, but is not guaranteed by us, may be incomplete and/or may change without notice.